tem description/product images



Description

Material:

Housing die-cast zinc.Worm screw and worm wheel steel.

Version:

Housing bright. Worm screw and worm wheel case hardened.

Note:


Compact, universally applicable and maintenance-free worm drive in one size with a centre distance of 25 mm and 4 different ratios. The rotation direction of the shaft is arbitrary. Compact design with maximum torque, ruggedness and smooth power transmission distinguish these gearboxes. A flexible screw mounting enables easy installation.

These worm gears are designed for manual operation.

Drive is provided by a 7 AF hexagon socket. Output via a 10 AF hexagon socket.

Drawing reference:

- 1) Drive
- 2) Output



Overview of items

| Order No. | Transmission ratio | Self-locking | Max. output torque M Nm |
|-------------|--------------------|------------------|-------------------------------|
| 22700-10-1 | 1:1 | not self-locking | 2 |
| 22700-10-2 | 2:1 | not self-locking | 3 |
| 22700-10-20 | 20:1 | self-locking | 15 |
| 22700-10-30 | 30:1 | self-locking | 17 |

Drawings

Overview of items