

Item description/product images



Description

Material:

Black thermoplastic.

Bush and screw grade 5.8 steel.

Version:

Steel trivalent blue-passivated.

Note:

For the inch series, dimension D is in inches, all other dimensions are in mm.

Drawing reference:

Form D: tapped bush without cap

Form K: tapped bush with cap

Form E: reamed bush without cap

Form H: reamed bush with cap

Form L: external thread

Overview of items

Knurled Wheels, internal thread, inch

Order No.	Form	D	D1	D2	H	H1	T
06266-11A1	D	10-32	40	16,5	31	13	10
06266-11A2	D	1/4-20	40	16,5	31	13	10
06266-11A3	D	5/16-18	40	16,5	31	13	14
06266-12A3	D	5/16-18	50	18	36	15	14
06266-12A4	D	3/8-16	50	18	36	15	14
06266-13A4	D	3/8-16	63	22	41	17	14
06266-13A5	D	1/2-13	63	22	41	17	18

Knurled Wheels, internal thread, inch

Order No.	Form	D	D1	D2	H	H1	T
06266-21A1Δ	K	10-32	40	16,5	31	13	10
06266-21A2Δ	K	1/4-20	40	16,5	31	13	10
06266-21A3Δ	K	5/16-18	40	16,5	31	13	14
06266-22A3Δ	K	5/16-18	50	18	36	15	14
06266-22A4Δ	K	3/8-16	50	18	36	15	14
06266-23A4Δ	K	3/8-16	63	22	41	17	14
06266-23A5Δ	K	1/2-13	63	22	41	17	18

Knurled Wheels, with bushing, inch

Order No.	Form	D	D1	D2	H	H1	T
06266-31CM	E	0,25	40	16,5	31	13	10
06266-32CN	E	0,312	50	18	36	15	14
06266-33CO	E	0,375	63	22	41	17	14

Knurled Wheels, with bushing, inch

Order No.	Form	Size	D	D1	D2	H	H1	T
06266-41CMΔ	H	1	0,25	40	16,5	31	13	10
06266-42CNΔ	H	2	0,312	50	18	36	15	14
06266-43COΔ	H	3	0,375	63	22	41	17	14

Overview of items

Knurled Wheels, external thread, inch

Order No.	Form	Size	D	D1	D2	H	H1	L
06266-51A1ΔX	L	1	10-32	40	16,5	31	13	10/20
06266-51A2ΔX	L	1	1/4-20	40	16,5	31	13	20/30
06266-51A3ΔX	L	1	5/16-18	40	16,5	31	13	20/40
06266-52A3ΔX	L	2	5/16-18	50	18	36	15	20/40
06266-52A4ΔX	L	2	3/8-16	50	18	36	15	20/40
06266-53A4ΔX	L	3	3/8-16	63	22	41	17	20/40
06266-53A5ΔX	L	3	1/2-13	63	22	41	17	30/60