

Item description/product images



Description

Material:

Reinforced thermoplastic polyamide, black-grey RAL 7021.
Steel parts grade 5.8 steel or 1.4305 stainless steel.

Version:

Metal parts trivalent blue passivated steel or bright stainless steel.

Note:

Palm grips with projecting steel bush and internal thread are highly suitable for cross pinning.

Application:

These palm grips have been specially developed for use in applications with high hygienic requirements. The closed grip contour with smooth surfaces are very easy to clean.

Advantages:

Resistant to humidity and cleaning products (during disinfection) with no toxic side effects (bio-compatible).

The palm grips can be tightened or loosened without tools.

Suitable for manual fixating and clamping. Various thread sizes.

On request:


Special versions.

Drawing reference:

Form K: tapped bush

Form L: external thread

Drawings



Overview of items

Order No.	Form	Component material	Surface finish component	Main colour	D	D1	D2	H	H2	H3	L	T
06174-250590	K	steel	blue-passivated	black grey	M5	25	10	18	9	7	-	9
06174-320690	K	steel	blue-passivated	black grey	M6	32	13,5	22	12	9,5	-	12
06174-400690	K	steel	blue-passivated	black grey	M6	40	13,5	26	14	10	-	12
06174-400890	K	steel	blue-passivated	black grey	M8	40	13,5	26	14	10	-	12
06174-500890	K	steel	blue-passivated	black grey	M8	50	19	32	18	12	-	17

Overview of items

Order No.	Form	Component material	Surface finish component	Main colour	D	D1	D2	H	H2	H3	L	T
06174-501090	K	steel	blue-passivated	black grey	M10	50	19	32	18	12	-	17
06174-631090	K	steel	blue-passivated	black grey	M10	63	19	38	21,5	12,5	-	17
06174-631290	K	steel	blue-passivated	black grey	M12	63	19	38	21,5	12,5	-	17
06174-631690	K	steel	blue-passivated	black grey	M16	63	19	38	21,5	12,5	-	17
06174-2505290	K	stainless steel	bright	black grey	M5	25	10	18	9	7	-	9
06174-3206290	K	stainless steel	bright	black grey	M6	32	13,5	22	12	9,5	-	12
06174-4006290	K	stainless steel	bright	black grey	M6	40	13,5	26	14	10	-	12
06174-4008290	K	stainless steel	bright	black grey	M8	40	13,5	26	14	10	-	12
06174-5008290	K	stainless steel	bright	black grey	M8	50	19	32	18	12	-	17
06174-5010290	K	stainless steel	bright	black grey	M10	50	19	32	18	12	-	17
06174-6310290	K	stainless steel	bright	black grey	M10	63	19	38	21,5	12,5	-	17
06174-6312290	K	stainless steel	bright	black grey	M12	63	19	38	21,5	12,5	-	17
06174-6316290	K	stainless steel	bright	black grey	M16	63	19	38	21,5	12,5	-	17
06174-250590X10	L	steel	blue-passivated	black grey	M5	25	10	18	9	7	10	-
06174-250590X15	L	steel	blue-passivated	black grey	M5	25	10	18	9	7	15	-
06174-250590X20	L	steel	blue-passivated	black grey	M5	25	10	18	9	7	20	-
06174-320690X10	L	steel	blue-passivated	black grey	M6	32	13,5	22	12	9,5	10	-
06174-320690X15	L	steel	blue-passivated	black grey	M6	32	13,5	22	12	9,5	15	-
06174-320690X20	L	steel	blue-passivated	black grey	M6	32	13,5	22	12	9,5	20	-
06174-320690X25	L	steel	blue-passivated	black grey	M6	32	13,5	22	12	9,5	25	-
06174-320690X30	L	steel	blue-passivated	black grey	M6	32	13,5	22	12	9,5	30	-
06174-400890X15	L	steel	blue-passivated	black grey	M8	40	13,5	26	14	10	15	-
06174-400890X20	L	steel	blue-passivated	black grey	M8	40	13,5	26	14	10	20	-
06174-400890X25	L	steel	blue-passivated	black grey	M8	40	13,5	26	14	10	25	-
06174-400890X30	L	steel	blue-passivated	black grey	M8	40	13,5	26	14	10	30	-
06174-400890X40	L	steel	blue-passivated	black grey	M8	40	13,5	26	14	10	40	-
06174-400890X50	L	steel	blue-passivated	black grey	M8	40	13,5	26	14	10	50	-
06174-501090X20	L	steel	blue-passivated	black grey	M10	50	19	32	18	12	20	-
06174-501090X25	L	steel	blue-passivated	black grey	M10	50	19	32	18	12	25	-
06174-501090X30	L	steel	blue-passivated	black grey	M10	50	19	32	18	12	30	-
06174-501090X40	L	steel	blue-passivated	black grey	M10	50	19	32	18	12	40	-
06174-501090X50	L	steel	blue-passivated	black grey	M10	50	19	32	18	12	50	-
06174-501090X60	L	steel	blue-passivated	black grey	M10	50	19	32	18	12	60	-
06174-631290X20	L	steel	blue-passivated	black grey	M12	63	19	38	21,5	12,5	20	-
06174-631290X25	L	steel	blue-passivated	black grey	M12	63	19	38	21,5	12,5	25	-
06174-631290X30	L	steel	blue-passivated	black grey	M12	63	19	38	21,5	12,5	30	-
06174-631290X40	L	steel	blue-passivated	black grey	M12	63	19	38	21,5	12,5	40	-
06174-631290X50	L	steel	blue-passivated	black grey	M12	63	19	38	21,5	12,5	50	-
06174-631290X60	L	steel	blue-passivated	black grey	M12	63	19	38	21,5	12,5	60	-
06174-2505290X10	L	stainless steel	bright	black grey	M5	25	10	18	9	7	10	-
06174-2505290X15	L	stainless steel	bright	black grey	M5	25	10	18	9	7	15	-
06174-2505290X20	L	stainless steel	bright	black grey	M5	25	10	18	9	7	20	-
06174-3206290X10	L	stainless steel	bright	black grey	M6	32	13,5	22	12	9,5	10	-
06174-3206290X15	L	stainless steel	bright	black grey	M6	32	13,5	22	12	9,5	15	-
06174-3206290X20	L	stainless steel	bright	black grey	M6	32	13,5	22	12	9,5	20	-
06174-3206290X25	L	stainless steel	bright	black grey	M6	32	13,5	22	12	9,5	25	-
06174-3206290X30	L	stainless steel	bright	black grey	M6	32	13,5	22	12	9,5	30	-
06174-4008290X15	L	stainless steel	bright	black grey	M8	40	13,5	26	14	10	15	-
06174-4008290X20	L	stainless steel	bright	black grey	M8	40	13,5	26	14	10	20	-
06174-4008290X25	L	stainless steel	bright	black grey	M8	40	13,5	26	14	10	25	-
06174-4008290X30	L	stainless steel	bright	black grey	M8	40	13,5	26	14	10	30	-
06174-4008290X40	L	stainless steel	bright	black grey	M8	40	13,5	26	14	10	40	-
06174-4008290X50	L	stainless steel	bright	black grey	M8	40	13,5	26	14	10	50	-
06174-5010290X20	L	stainless steel	bright	black grey	M10	50	19	32	18	12	20	-
06174-5010290X25	L	stainless steel	bright	black grey	M10	50	19	32	18	12	25	-
06174-5010290X30	L	stainless steel	bright	black grey	M10	50	19	32	18	12	30	-
06174-5010290X40	L	stainless steel	bright	black grey	M10	50	19	32	18	12	40	-
06174-5010290X50	L	stainless steel	bright	black grey	M10	50	19	32	18	12	50	-
06174-5010290X60	L	stainless steel	bright	black grey	M10	50	19	32	18	12	60	-
06174-6312290X20	L	stainless steel	bright	black grey	M12	63	19	38	21,5	12,5	20	-
06174-6312290X25	L	stainless steel	bright	black grey	M12	63	19	38	21,5	12,5	25	-
06174-6312290X30	L	stainless steel	bright	black grey	M12	63	19	38	21,5	12,5	30	-
06174-6312290X40	L	stainless steel	bright	black grey	M12	63	19	38	21,5	12,5	40	-
06174-6312290X50	L	stainless steel	bright	black grey	M12	63	19	38	21,5	12,5	50	-
06174-6312290X60	L	stainless steel	bright	black grey	M12	63	19	38	21,5	12,5	60	-

