

Item description/product images

**Description****Material:**

Thermoplastic, black grey.
Bush and screw stainless steel 1.4305.

Version:

Stainless steel bright.

Drawing reference:

Form D: tapped bush without cap


Form K: tapped bush with cap

Form L: external thread


Item description/product images



Item description/product images



Drawings



Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06267-1105	D	-	1	M5	40	16,5	30	13	10	-
06267-1106	D	-	1	M6	40	16,5	30	13	10	-
06267-1108	D	-	1	M8	40	16,5	30	13	14	-
06267-1208	D	-	2	M8	50	18	35	15	14	-
06267-1210	D	-	2	M10	50	18	35	15	14	-
06267-1310	D	-	3	M10	63	22	40	17	14	-
06267-1312	D	-	3	M12	63	22	40	17	18	-
06267-2105	K	black grey RAL 7021	1	M5	40	16,5	31	13	10	-
06267-21051	K	orange RAL 2004	1	M5	40	16,5	31	13	10	-
06267-21052	K	signal green RAL6032	1	M5	40	16,5	31	13	10	-
06267-21053	K	blue RAL5017	1	M5	40	16,5	31	13	10	-
06267-21055	K	light grey RAL 7035	1	M5	40	16,5	31	13	10	-
06267-21056	K	traffic red RAL 3020	1	M5	40	16,5	31	13	10	-
06267-21057	K	colza yellow RAL 1021	1	M5	40	16,5	31	13	10	-

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06267-2106	K	black grey RAL 7021	1	M6	40	16,5	31	13	10	-
06267-21061	K	orange RAL 2004	1	M6	40	16,5	31	13	10	-
06267-21062	K	signal green RAL6032	1	M6	40	16,5	31	13	10	-
06267-21063	K	blue RAL5017	1	M6	40	16,5	31	13	10	-
06267-21065	K	light grey RAL 7035	1	M6	40	16,5	31	13	10	-
06267-21066	K	traffic red RAL 3020	1	M6	40	16,5	31	13	10	-
06267-21067	K	colza yellow RAL 1021	1	M6	40	16,5	31	13	10	-
06267-2108	K	black grey RAL 7021	1	M8	40	16,5	31	13	14	-
06267-21081	K	orange RAL 2004	1	M8	40	16,5	31	13	10	-
06267-21082	K	signal green RAL6032	1	M8	40	16,5	31	13	10	-
06267-21083	K	blue RAL5017	1	M8	40	16,5	31	13	10	-
06267-21085	K	light grey RAL 7035	1	M8	40	16,5	31	13	14	-
06267-21086	K	traffic red RAL 3020	1	M8	40	16,5	31	13	14	-
06267-21087	K	colza yellow RAL 1021	1	M8	40	16,5	31	13	14	-
06267-2208	K	black grey RAL 7021	2	M8	50	18	36	15	14	-
06267-22081	K	orange RAL 2004	2	M8	50	18	36	15	14	-
06267-22082	K	signal green RAL6032	2	M8	50	18	36	15	14	-
06267-22083	K	blue RAL5017	2	M8	50	18	36	15	14	-
06267-22085	K	light grey RAL 7035	2	M8	50	18	36	15	14	-
06267-22086	K	traffic red RAL 3020	2	M8	50	18	36	15	14	-
06267-22087	K	colza yellow RAL 1021	2	M8	50	18	36	15	14	-
06267-2210	K	black grey RAL 7021	2	M10	50	18	36	15	14	-
06267-22101	K	orange RAL 2004	2	M10	50	18	36	15	14	-
06267-22102	K	signal green RAL6032	2	M10	50	18	36	15	14	-
06267-22103	K	blue RAL5017	2	M10	50	18	36	15	14	-
06267-22105	K	light grey RAL 7035	2	M10	50	18	36	15	14	-
06267-22106	K	traffic red RAL 3020	2	M10	50	18	36	15	14	-
06267-22107	K	colza yellow RAL 1021	2	M10	50	18	36	15	14	-
06267-2310	K	black grey RAL 7021	3	M10	63	22	41	17	14	-
06267-23101	K	orange RAL 2004	3	M10	63	22	41	17	14	-
06267-23102	K	signal green RAL6032	3	M10	63	22	41	17	14	-
06267-23103	K	blue RAL5017	3	M10	63	22	41	17	14	-
06267-23105	K	light grey RAL 7035	3	M10	63	22	41	17	14	-
06267-23106	K	traffic red RAL 3020	3	M10	63	22	41	17	14	-
06267-23107	K	colza yellow RAL 1021	3	M10	63	22	41	17	14	-
06267-2312	K	black grey RAL 7021	3	M12	63	22	41	17	18	-
06267-23121	K	orange RAL 2004	3	M12	63	22	41	17	18	-
06267-23122	K	signal green RAL6032	3	M12	63	22	41	17	18	-
06267-23123	K	blue RAL5017	3	M12	63	22	41	17	18	-
06267-23125	K	light grey RAL 7035	3	M12	63	22	41	17	18	-
06267-23126	K	traffic red RAL 3020	3	M12	63	22	41	17	18	-
06267-23127	K	colza yellow RAL 1021	3	M12	63	22	41	17	18	-
06267-5105ΔX	L	black grey RAL 7021	1	M5	40	16,5	31	13	-	10
06267-51051X10	L	orange RAL 2004	1	M5	40	16,5	31	13	-	10
06267-51052X10	L	signal green RAL6032	1	M5	40	16,5	31	13	-	10
06267-51053X10	L	blue RAL5017	1	M5	40	16,5	31	13	-	10
06267-51055X10	L	light grey RAL 7035	1	M5	40	16,5	31	13	-	10
06267-51056X10	L	traffic red RAL 3020	1	M5	40	16,5	31	13	-	10
06267-51057X10	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	-	10
06267-5105ΔX	L	black grey RAL 7021	1	M5	40	16,5	31	13	-	20
06267-51051X20	L	orange RAL 2004	1	M5	40	16,5	31	13	-	20
06267-51052X20	L	signal green RAL6032	1	M5	40	16,5	31	13	-	20
06267-51053X20	L	blue RAL5017	1	M5	40	16,5	31	13	-	20
06267-51055X20	L	light grey RAL 7035	1	M5	40	16,5	31	13	-	20
06267-51056X20	L	traffic red RAL 3020	1	M5	40	16,5	31	13	-	20
06267-51057X20	L	colza yellow RAL 1021	1	M5	40	16,5	31	13	-	20
06267-5106ΔX	L	black grey RAL 7021	1	M6	40	16,5	31	13	-	10
06267-51061X10	L	orange RAL 2004	1	M6	40	16,5	31	13	-	10
06267-51062X10	L	signal green RAL6032	1	M6	40	16,5	31	13	-	10
06267-51063X10	L	blue RAL5017	1	M6	40	16,5	31	13	-	10
06267-51065X10	L	light grey RAL 7035	1	M6	40	16,5	31	13	-	10
06267-51066X10	L	traffic red RAL 3020	1	M6	40	16,5	31	13	-	10
06267-51067X10	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	-	10
06267-5106ΔX	L	black grey RAL 7021	1	M6	40	16,5	31	13	-	20
06267-51061X20	L	orange RAL 2004	1	M6	40	16,5	31	13	-	20

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06267-51062X20	L	signal green RAL6032	1	M6	40	16,5	31	13	-	20
06267-51063X20	L	blue RAL5017	1	M6	40	16,5	31	13	-	20
06267-51065X20	L	light grey RAL 7035	1	M6	40	16,5	31	13	-	20
06267-51066X20	L	traffic red RAL 3020	1	M6	40	16,5	31	13	-	20
06267-51067X20	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	-	20
06267-5106ΔX	L	black grey RAL 7021	1	M6	40	16,5	31	13	-	40
06267-51061X40	L	orange RAL 2004	1	M6	40	16,5	31	13	-	40
06267-51062X40	L	signal green RAL6032	1	M6	40	16,5	31	13	-	40
06267-51063X40	L	blue RAL5017	1	M6	40	16,5	31	13	-	40
06267-51065X40	L	light grey RAL 7035	1	M6	40	16,5	31	13	-	40
06267-51066X40	L	traffic red RAL 3020	1	M6	40	16,5	31	13	-	40
06267-51067X40	L	colza yellow RAL 1021	1	M6	40	16,5	31	13	-	40
06267-5108ΔX	L	black grey RAL 7021	1	M8	40	16,5	31	13	-	15
06267-51081X15	L	orange RAL 2004	1	M8	40	16,5	31	13	-	15
06267-51082X15	L	signal green RAL6032	1	M8	40	16,5	31	13	-	15
06267-51083X15	L	blue RAL5017	1	M8	40	16,5	31	13	-	15
06267-51085X15	L	light grey RAL 7035	1	M8	40	16,5	31	13	-	15
06267-51086X15	L	traffic red RAL 3020	1	M8	40	16,5	31	13	-	15
06267-51087X15	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	-	15
06267-5108ΔX	L	black grey RAL 7021	1	M8	40	16,5	31	13	-	30
06267-51081X30	L	orange RAL 2004	1	M8	40	16,5	31	13	-	30
06267-51082X30	L	signal green RAL6032	1	M8	40	16,5	31	13	-	30
06267-51083X30	L	blue RAL5017	1	M8	40	16,5	31	13	-	30
06267-51085X30	L	light grey RAL 7035	1	M8	40	16,5	31	13	-	30
06267-51086X30	L	traffic red RAL 3020	1	M8	40	16,5	31	13	-	30
06267-51087X30	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	-	30
06267-5108ΔX	L	black grey RAL 7021	1	M8	40	16,5	31	13	-	60
06267-51081X60	L	orange RAL 2004	1	M8	40	16,5	31	13	-	60
06267-51082X60	L	signal green RAL6032	1	M8	40	16,5	31	13	-	60
06267-51083X60	L	blue RAL5017	1	M8	40	16,5	31	13	-	60
06267-51085X60	L	light grey RAL 7035	1	M8	40	16,5	31	13	-	60
06267-51086X60	L	traffic red RAL 3020	1	M8	40	16,5	31	13	-	60
06267-51087X60	L	colza yellow RAL 1021	1	M8	40	16,5	31	13	-	60
06267-5208ΔX	L	black grey RAL 7021	2	M8	50	18	36	15	-	15
06267-52081X15	L	orange RAL 2004	2	M8	50	18	36	15	-	15
06267-52082X15	L	signal green RAL6032	2	M8	50	18	36	15	-	15
06267-52083X15	L	blue RAL5017	2	M8	50	18	36	15	-	15
06267-52085X15	L	light grey RAL 7035	2	M8	50	18	36	15	-	15
06267-52086X15	L	traffic red RAL 3020	2	M8	50	18	36	15	-	15
06267-52087X15	L	colza yellow RAL 1021	2	M8	50	18	36	15	-	15
06267-5208ΔX	L	black grey RAL 7021	2	M8	50	18	36	15	-	30
06267-52081X30	L	orange RAL 2004	2	M8	50	18	36	15	-	30
06267-52082X30	L	signal green RAL6032	2	M8	50	18	36	15	-	30
06267-52083X30	L	blue RAL5017	2	M8	50	18	36	15	-	30
06267-52085X30	L	light grey RAL 7035	2	M8	50	18	36	15	-	30
06267-52086X30	L	traffic red RAL 3020	2	M8	50	18	36	15	-	30
06267-52087X30	L	colza yellow RAL 1021	2	M8	50	18	36	15	-	30
06267-5208ΔX	L	black grey RAL 7021	2	M8	50	18	36	15	-	60
06267-52081X60	L	orange RAL 2004	2	M8	50	18	36	15	-	60
06267-52082X60	L	signal green RAL6032	2	M8	50	18	36	15	-	60
06267-52083X60	L	blue RAL5017	2	M8	50	18	36	15	-	60
06267-52085X60	L	light grey RAL 7035	2	M8	50	18	36	15	-	60
06267-52086X60	L	traffic red RAL 3020	2	M8	50	18	36	15	-	60
06267-52087X60	L	colza yellow RAL 1021	2	M8	50	18	36	15	-	60
06267-5210ΔX	L	black grey RAL 7021	2	M10	50	18	36	15	-	20
06267-52101X20	L	orange RAL 2004	2	M10	50	18	36	15	-	20
06267-52102X20	L	signal green RAL6032	2	M10	50	18	36	15	-	20
06267-52103X20	L	blue RAL5017	2	M10	50	18	36	15	-	20
06267-52105X20	L	light grey RAL 7035	2	M10	50	18	36	15	-	20
06267-52106X20	L	traffic red RAL 3020	2	M10	50	18	36	15	-	20
06267-52107X20	L	colza yellow RAL 1021	2	M10	50	18	36	15	-	20
06267-5210ΔX	L	black grey RAL 7021	2	M10	50	18	36	15	-	30
06267-52101X30	L	orange RAL 2004	2	M10	50	18	36	15	-	30
06267-52102X30	L	signal green RAL6032	2	M10	50	18	36	15	-	30
06267-52103X30	L	blue RAL5017	2	M10	50	18	36	15	-	30

Overview of items

Order No.	Form	Colour Cap	Size	D	D1	D2	H	H1	T	L
06267-52105X30	L	light grey RAL 7035	2	M10	50	18	36	15	-	30
06267-52106X30	L	traffic red RAL 3020	2	M10	50	18	36	15	-	30
06267-52107X30	L	colza yellow RAL 1021	2	M10	50	18	36	15	-	30
06267-5210ΔX	L	black grey RAL 7021	2	M10	50	18	36	15	-	60
06267-52101X60	L	orange RAL 2004	2	M10	50	18	36	15	-	60
06267-52102X60	L	signal green RAL6032	2	M10	50	18	36	15	-	60
06267-52103X60	L	blue RAL5017	2	M10	50	18	36	15	-	60
06267-52105X60	L	light grey RAL 7035	2	M10	50	18	36	15	-	60
06267-52106X60	L	traffic red RAL 3020	2	M10	50	18	36	15	-	60
06267-52107X60	L	colza yellow RAL 1021	2	M10	50	18	36	15	-	60
06267-5310ΔX	L	black grey RAL 7021	3	M10	63	22	41	17	-	20
06267-53101X20	L	orange RAL 2004	3	M10	63	22	41	17	-	20
06267-53102X20	L	signal green RAL6032	3	M10	63	22	41	17	-	20
06267-53103X20	L	blue RAL5017	3	M10	63	22	41	17	-	20
06267-53105X20	L	light grey RAL 7035	3	M10	63	22	41	17	-	20
06267-53106X20	L	traffic red RAL 3020	3	M10	63	22	41	17	-	20
06267-53107X20	L	colza yellow RAL 1021	3	M10	63	22	41	17	-	20
06267-5310ΔX	L	black grey RAL 7021	3	M10	63	22	41	17	-	30
06267-53101X30	L	orange RAL 2004	3	M10	63	22	41	17	-	30
06267-53102X30	L	signal green RAL6032	3	M10	63	22	41	17	-	30
06267-53103X30	L	blue RAL5017	3	M10	63	22	41	17	-	30
06267-53105X30	L	light grey RAL 7035	3	M10	63	22	41	17	-	30
06267-53106X30	L	traffic red RAL 3020	3	M10	63	22	41	17	-	30
06267-53107X30	L	colza yellow RAL 1021	3	M10	63	22	41	17	-	30
06267-5310ΔX	L	black grey RAL 7021	3	M10	63	22	41	17	-	60
06267-53101X60	L	orange RAL 2004	3	M10	63	22	41	17	-	60
06267-53102X60	L	signal green RAL6032	3	M10	63	22	41	17	-	60
06267-53103X60	L	blue RAL5017	3	M10	63	22	41	17	-	60
06267-53105X60	L	light grey RAL 7035	3	M10	63	22	41	17	-	60
06267-53106X60	L	traffic red RAL 3020	3	M10	63	22	41	17	-	60
06267-53107X60	L	colza yellow RAL 1021	3	M10	63	22	41	17	-	60