

## Item description/product images



## Description

**Material:**

Steel.

**Version:**

Case-hardened and ground.


Paired height tolerance 0.004 mm, nominal dimension height tolerance of  $\pm 0.004$  mm.

B and L nominal dimension tolerances acc. to DIN ISO 2768-m.

**Note:**

The parallel block set is supplied in a wooden box with removable lid.

## Drawings



## Overview of items

Order No.	Contents 1 pair of each H x B x L	H paired tolerance T	H nom. dim. tolerance
03212-01	14x10x150, 16x10x150, 18x10x150, 20x10x150, 22x10x150, 24x10x150, 26x10x150, 28x10x150, 30x10x150, 32x10x150, 35x10x150, 40x10x150,	0,004	$\pm 0,004$