

## Item description/product images



## Description

**Material:**

Housing steel tube filled with steel balls.  
 Shaft steel tube with rubber grip or Hickory.  
 Inserts white nylon (grease and oil resistant).

**Note:**

Inserts to reorder 96614.



## Overview of items

Order No.	Version 1	Head-Ø	H=Height	L=Length
96610-03001	with wooden shaft	30	110	330
96610-04001	with wooden shaft	40	115	360
96610-05001	with wooden shaft	50	120	370
96610-06001	with wooden shaft	60	145	370
96610-03002	with steel tube shaft	30	110	290
96610-04002	with steel tube shaft	40	115	300
96610-05002	with steel tube shaft	50	120	310
96610-06002	with steel tube shaft	60	145	325