

tem description/product images



Description

Material:

Race body die-cast aluminium.

End pieces polyester.

Wipers modified polyamide.

longitudinal seals rubber.

Rollers steel 1.3505.

Version:

Runner body nickel-plated.

Note:

Roller carriage with lifetime lubricated ball bearings and patented wiper technology which lubricates the system while in motion.

A simple adjustment of the middle roller makes the roller carriage play-free or sets the desired preload in the rail.

High traverse speeds of up to 7 m/s and extremely quiet (faster and quieter than systems with recycling ball bearings).

Application temperature -30 °C to +120 °C.


On request:

Roller carriages with 4 or 5 rollers.

Note:

Carriages size 18 (fixed bearing and floating bearing) do not have grease nipples.

Drawings



Overview of items

© norelem www.norelem.com

21322 Roller carriages aluminium



Overview of items

© norelem www.norelem.com 2/2