

Item description/product images



Description

Overview of items

Order No.	Image	Article description
33058-015		PROBE HARDENED STEEL
33058-020		PROBE HARDENED STEEL
33058-025		PROBE HARDENED STEEL
33058-030		PROBE HARDENED STEEL
33058-035		PROBE HARDENED STEEL
33058-040		PROBE HARDENED STEEL

Overview of items

Order No.	Image	Article description
33058-045		PROBE HARDENED STEEL
33058-050		PROBE HARDENED STEEL
33058-055		PROBE HARDENED STEEL
33058-060		PROBE HARDENED STEEL
33058-065		PROBE HARDENED STEEL
33058-070		PROBE HARDENED STEEL
33058-075		PROBE HARDENED STEEL

Overview of items

Order No.	Image	Article description
	<p>Technical drawing of a probe insert. It shows two views: a side view and a front view. The side view shows a total length of 22, a diameter of 4 at the tip, and a diameter of 8 at the top. The front view shows a diameter of 15.</p>	
33058-080	<p>Technical drawing of a probe insert. It shows two views: a side view and a front view. The side view shows a total length of 16, a diameter of 5 at the tip, and a diameter of 8 at the top. The front view shows a 27-degree angle.</p>	PROBE HARDENED STEEL
33058-085	<p>Technical drawing of a probe insert. It shows a side view with a total length of 10, a diameter of Ø5 at the tip, and a 60-degree angle.</p>	PROBE HARDENED STEEL
33058-090	<p>Technical drawing of a probe insert. It shows a side view with a diameter of Ø1/8\" at the tip, a diameter of Ø5 at the base, and a length of 6.</p>	PROBE HARDENED STEEL