

## Item description/product images



## Description

**Material:**

Grip aluminium EN AW-6060.  
Legs glass-bead reinforced polyamide.

**Version:**

Grip natural colour anodised or with black serrated plastic cover.

**Note:**


The legs have 2 or 4 PVC profile pins in the hole for the grip tube. When pushing the tube in these are trimmed off and produce a precise seating.

Black electro zinc-plated fastening screws, suitable washers and nuts are supplied.

**Assembly:**

From the front.

## Drawings



## Overview of items

| Order No.    | Main colour | Form | A   | B  | D     | H    | L   | Load capacity N |
|--------------|-------------|------|-----|----|-------|------|-----|-----------------|
| 06939-150203 | natural     | A    | 150 | 32 | M5x20 | 55,5 | 184 | 1000            |
| 06939-200203 | natural     | A    | 200 | 32 | M5x20 | 55,5 | 234 | 1000            |
| 06939-300203 | natural     | A    | 300 | 32 | M5x20 | 55,5 | 334 | 1000            |
| 06939-400203 | natural     | A    | 400 | 32 | M5x20 | 55,5 | 434 | 1000            |
| 06939-500203 | natural     | A    | 500 | 32 | M5x20 | 55,5 | 534 | 1000            |
| 06939-150202 | black       | A    | 150 | 32 | M5x20 | 55,5 | 184 | 1000            |
| 06939-200202 | black       | A    | 200 | 32 | M5x20 | 55,5 | 234 | 1000            |
| 06939-300202 | black       | A    | 300 | 32 | M5x20 | 55,5 | 334 | 1000            |
| 06939-400202 | black       | A    | 400 | 32 | M5x20 | 55,5 | 434 | 1000            |
| 06939-500202 | black       | A    | 500 | 32 | M5x20 | 55,5 | 534 | 1000            |
| 06939-150302 | black       | B    | 150 | 48 | M8x25 | 80   | 200 | 1000            |
| 06939-300302 | black       | B    | 300 | 48 | M8x25 | 80   | 350 | 1000            |
| 06939-400302 | black       | B    | 400 | 48 | M8x25 | 80   | 450 | 1000            |
| 06939-200302 | black       | B    | 200 | 48 | M8x25 | 80   | 250 | 1000            |
| 06939-400303 | natural     | B    | 400 | 48 | M8x25 | 80   | 450 | 1000            |
| 06939-500303 | natural     | B    | 500 | 48 | M8x25 | 80   | 550 | 1000            |
| 06939-300303 | natural     | B    | 300 | 48 | M8x25 | 80   | 350 | 1000            |
| 06939-500302 | black       | B    | 500 | 48 | M8x25 | 80   | 550 | 1000            |
| 06939-150303 | natural     | B    | 150 | 48 | M8x25 | 80   | 200 | 1000            |
| 06939-200303 | natural     | B    | 200 | 48 | M8x25 | 80   | 250 | 1000            |