

Item description/product images



Description


Material:

Black thermoplastic.


Screw grade 5.8 steel or 1.4305 stainless steel.

Version:

Steel trivalent blue passivated, stainless steel bright.



Drawings



Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	L
06242-04X10	steel	black grey RAL 7021	M4	21	12	19	21	10	10
06242-041X10	steel	orange RAL 2004	M4	21	12	19	21	10	10
06242-042X10	steel	signal green RAL6032	M4	21	12	19	21	10	10
06242-043X10	steel	blue RAL5017	M4	21	12	19	21	10	10
06242-045X10	steel	light grey RAL 7035	M4	21	12	19	21	10	10
06242-046X10	steel	traffic red RAL 3020	M4	21	12	19	21	10	10
06242-047X10	steel	colza yellow RAL 1021	M4	21	12	19	21	10	10
06242-05X10	steel	black grey RAL 7021	M5	21	12	19	21	10	10
06242-051X10	steel	orange RAL 2004	M5	21	12	19	21	10	10
06242-052X10	steel	signal green RAL6032	M5	21	12	19	21	10	10
06242-053X10	steel	blue RAL5017	M5	21	12	19	21	10	10

## Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	H	H1	L
06242-055X10	steel	light grey RAL 7035	M5	21	12	19	21	10	10
06242-056X10	steel	traffic red RAL 3020	M5	21	12	19	21	10	10
06242-057X10	steel	colza yellow RAL 1021	M5	21	12	19	21	10	10
06242-061X15	steel	black grey RAL 7021	M6	25	14	23	25	12	15
06242-061X15	steel	orange RAL 2004	M6	25	14	23	25	12	15
06242-062X15	steel	signal green RAL6032	M6	25	14	23	25	12	15
06242-063X15	steel	blue RAL5017	M6	25	14	23	25	12	15
06242-065X15	steel	light grey RAL 7035	M6	25	14	23	25	12	15
06242-066X15	steel	traffic red RAL 3020	M6	25	14	23	25	12	15
06242-067X15	steel	colza yellow RAL 1021	M6	25	14	23	25	12	15
06242-081X15	steel	black grey RAL 7021	M8	33	18	31	33	15	15
06242-081X15	steel	orange RAL 2004	M8	33	18	31	33	15	15
06242-082X15	steel	signal green RAL6032	M8	33	18	31	33	15	15
06242-083X15	steel	blue RAL5017	M8	33	18	31	33	15	15
06242-085X15	steel	light grey RAL 7035	M8	33	18	31	33	15	15
06242-086X15	steel	traffic red RAL 3020	M8	33	18	31	33	15	15
06242-087X15	steel	colza yellow RAL 1021	M8	33	18	31	33	15	15
06242-004X10	stainless steel	black grey RAL 7021	M4	21	12	19	21	10	10
06242-0041X10	stainless steel	orange RAL 2004	M4	21	12	19	21	10	10
06242-0042X10	stainless steel	signal green RAL6032	M4	21	12	19	21	10	10
06242-0043X10	stainless steel	blue RAL5017	M4	21	12	19	21	10	10
06242-0045X10	stainless steel	light grey RAL 7035	M4	21	12	19	21	10	10
06242-0046X10	stainless steel	traffic red RAL 3020	M4	21	12	19	21	10	10
06242-0047X10	stainless steel	colza yellow RAL 1021	M4	21	12	19	21	10	10
06242-005X10	stainless steel	black grey RAL 7021	M5	21	12	19	21	10	10
06242-0051X10	stainless steel	orange RAL 2004	M5	21	12	19	21	10	10
06242-0052X10	stainless steel	signal green RAL6032	M5	21	12	19	21	10	10
06242-0053X10	stainless steel	blue RAL5017	M5	21	12	19	21	10	10
06242-0055X10	stainless steel	light grey RAL 7035	M5	21	12	19	21	10	10
06242-0056X10	stainless steel	traffic red RAL 3020	M5	21	12	19	21	10	10
06242-0057X10	stainless steel	colza yellow RAL 1021	M5	21	12	19	21	10	10
06242-006X15	stainless steel	black grey RAL 7021	M6	25	14	23	25	12	15
06242-0061X15	stainless steel	orange RAL 2004	M6	25	14	23	25	12	15
06242-0062X15	stainless steel	signal green RAL6032	M6	25	14	23	25	12	15
06242-0063X15	stainless steel	blue RAL5017	M6	25	14	23	25	12	15
06242-0065X15	stainless steel	light grey RAL 7035	M6	25	14	23	25	12	15
06242-0066X15	stainless steel	traffic red RAL 3020	M6	25	14	23	25	12	15
06242-0067X15	stainless steel	colza yellow RAL 1021	M6	25	14	23	25	12	15
06242-008X15	stainless steel	black grey RAL 7021	M8	33	18	31	33	15	15
06242-0081X15	stainless steel	orange RAL 2004	M8	33	18	31	33	15	15
06242-0082X15	stainless steel	signal green RAL6032	M8	33	18	31	33	15	15
06242-0083X15	stainless steel	blue RAL5017	M8	33	18	31	33	15	15
06242-0085X15	stainless steel	light grey RAL 7035	M8	33	18	31	33	15	15
06242-0086X15	stainless steel	traffic red RAL 3020	M8	33	18	31	33	15	15
06242-0087X15	stainless steel	colza yellow RAL 1021	M8	33	18	31	33	15	15