


Item description/product images



Description


Material:

Thermoplastic, black grey.
Axis steel 5.8 or stainless steel 1.4305.

Version:

Trivalent blue passivated steel or bright stainless steel.
Circlips electro zinc-plated, including stainless steel version.

Drawings



Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	L	L2	L3	L4	SW
06246-106	steel	black grey RAL 7021	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-1061	steel	orange RAL 2004	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-1062	steel	signal green RAL6032	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-1063	steel	blue RAL5017	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-1065	steel	light grey RAL 7035	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-1066	steel	traffic red RAL 3020	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-1067	steel	colza yellow RAL 1021	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-208	steel	black grey RAL 7021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-2081	steel	orange RAL 2004	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-2082	steel	signal green RAL6032	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-2083	steel	blue RAL5017	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-2085	steel	light grey RAL 7035	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-2086	steel	traffic red RAL 3020	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-2087	steel	colza yellow RAL 1021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-310	steel	black grey RAL 7021	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-3101	steel	orange RAL 2004	M10	40	19	23	13	41	4	3	15	25	7	10	10

Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	L	L2	L3	L4	SW
06246-3102	steel	signal green RAL6032	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-3103	steel	blue RAL5017	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-3105	steel	light grey RAL 7035	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-3106	steel	traffic red RAL 3020	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-3107	steel	colza yellow RAL 1021	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-412	steel	black grey RAL 7021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-4121	steel	orange RAL 2004	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-4122	steel	signal green RAL6032	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-4123	steel	blue RAL5017	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-4125	steel	light grey RAL 7035	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-4126	steel	traffic red RAL 3020	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-4127	steel	colza yellow RAL 1021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-0106	stainless steel	black grey RAL 7021	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-01061	stainless steel	orange RAL 2004	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-01062	stainless steel	signal green RAL6032	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-01063	stainless steel	blue RAL5017	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-01065	stainless steel	light grey RAL 7035	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-01066	stainless steel	traffic red RAL 3020	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-01067	stainless steel	colza yellow RAL 1021	M6	25	12	17	8	25	3	2	10	15	5	5	7
06246-0208	stainless steel	black grey RAL 7021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-02081	stainless steel	orange RAL 2004	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-02082	stainless steel	signal green RAL6032	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-02083	stainless steel	blue RAL5017	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-02085	stainless steel	light grey RAL 7035	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-02086	stainless steel	traffic red RAL 3020	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-02087	stainless steel	colza yellow RAL 1021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
06246-0310	stainless steel	black grey RAL 7021	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-03101	stainless steel	orange RAL 2004	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-03102	stainless steel	signal green RAL6032	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-03103	stainless steel	blue RAL5017	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-03105	stainless steel	light grey RAL 7035	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-03106	stainless steel	traffic red RAL 3020	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-03107	stainless steel	colza yellow RAL 1021	M10	40	19	23	13	41	4	3	15	25	7	10	10
06246-0412	stainless steel	black grey RAL 7021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-04121	stainless steel	orange RAL 2004	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-04122	stainless steel	signal green RAL6032	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-04123	stainless steel	blue RAL5017	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-04125	stainless steel	light grey RAL 7035	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-04126	stainless steel	traffic red RAL 3020	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
06246-04127	stainless steel	colza yellow RAL 1021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13