

Item description/product images



Description

Material:

GJL 300.

Version:

Reference surfaces precision machined.

The clamping surfaces have 0.5 mm allowance.

Note:


Grid hole pitch 50 ± 0.01 mm.

Grid hole plugs and ring bolts for lifting are supplied.

A cover prevents the cavities of the tombstones filling with swarf. Workpieces can be mounted on all four clamping surfaces directly or using fixtures. Code numbers on the clamping surfaces prevent mounting the wrong part on the wrong face when different workpieces are being machined. The cube tombstones are matched to subplates for machine tools acc. to DIN 55201 and JIS 6337-1980.


Other dimensions on request.

Drawings




Drawings


01850-1240251




01850-1250301
01850-1650301



01850-126335
01850-166335



01850-168050



Overview of items

