


Technical information for structural dampers

Characteristic curves for constant load


26184-02917

Force – characteristic curve path, static
 E_{tot} : 0.75 Nm, E_{abs} : 0.14 Nm, efficiency: 19 %




26184-02917

Force – characteristic curve path, dynamic
 E_{tot} : 1.19 Nm, E_{abs} : 0.38 Nm, efficiency: 32 %




26184-03722

Force – characteristic curve path, static
 E_{tot} : 1.65 Nm, E_{abs} : 0.27 Nm, efficiency: 16 %




26184-03722

Force – characteristic curve path, dynamic
 E_{tot} : 2.26 Nm, E_{abs} : 0.63 Nm, efficiency: 28 %




26184-04325

Force – characteristic curve path, static
 E_{tot} : 2.36 Nm, E_{abs} : 0.38 Nm, efficiency: 16 %




26184-04325

Force – characteristic curve path, dynamic
 E_{tot} : 3.48 Nm, E_{abs} : 1.09 Nm, efficiency: 31 %




26184-05035

Force – characteristic curve path, static
 E_{tot} : 3.44 Nm, E_{abs} : 0.58 Nm, efficiency: 17 %




26184-05035

Force – characteristic curve path, dynamic
 E_{tot} : 5.8 Nm, E_{abs} : 2 Nm, efficiency: 34 %




26184-06343

Force – characteristic curve path, static
 E_{tot} : 8.77 Nm, E_{abs} : 1.45 Nm, efficiency: 17 %




26184-06343

Force – characteristic curve path, dynamic
 E_{tot} : 11.8 Nm, E_{abs} : 4 Nm, efficiency: 34 %




26184-06740

Force – characteristic curve path, static
E_{tot}: 17.5 Nm, E_{abs}: 2.7 Nm, efficiency: 15 %




26184-06740

Force – characteristic curve path, dynamic
E_{tot}: 23 Nm, E_{abs}: 6.2 Nm, efficiency: 27 %




26184-07646

Force – characteristic curve path, static
E_{tot}: 26.6 Nm, E_{abs}: 4.4 Nm, efficiency: 17 %




26184-07646

Force – characteristic curve path, dynamic
E_{tot}: 34.5 Nm, E_{abs}: 9.1 Nm, efficiency: 26 %




26184-08350

Force – characteristic curve path, static
E_{tot}: 35.4 Nm, E_{abs}: 6 Nm, efficiency: 17 %




26184-08350

Force – characteristic curve path, dynamic
E_{tot}: 45 Nm, E_{abs}: 12 Nm, efficiency: 27 %



26184-08550

Force – characteristic curve path, static
 E_{tot} : 49.7 Nm, E_{abs} : 8.3 Nm, efficiency: 17 %



26184-08550

Force – characteristic curve path, dynamic
 E_{tot} : 68 Nm, E_{abs} : 18 Nm, efficiency: 26 %

