


Item description/product images




Description


Material:
GJL 250 annealed.

Note:
The length L is cut by saw and is always supplied overlong.

Drawing reference:
machined faces: ± 0.25 mm
unmachined faces: ± 2 mm
length tolerance:
 ≤ 200 mm: $+3/+10$
 > 200 mm ≤ 590 mm: $+8/+15$
 ≥ 600 mm: $+20/+50$



Drawings



Overview of items

Order No.	L = length	B	H	≈ S	R
01760-01X	100/200	80	63	12	6
01760-02X	200/400	100	80	16	8
01760-03X	200/300/600	160	100	22	10

Overview of items

Order No.	L = length	B	H	≈ S	R
01760-04X	200/300/600	200	160	25	16
01760-05X	300/600	250	200	28	20