

Technical information

Quick clamping - reliable fixing

Durable and reliable

Now even more durable, more user-friendly and safer. This is the design aim that has been achieved in the new generation. You, the user, will notice the difference immediately: On first contact, the new toggle clamp has a good grip and is robust. It delivers fast, reliable and safe operation. High quality material ensures the necessary holding power.



Advantages:

Impressively stable:

All models can easily withstand 300,000 clamping cycles

Durable:

High-quality bushings - without scoring

Extremely robust:

Corrosion-resistant NITROX COATING or stainless steel

Simple design

The fixed top nut eases spindle adjustment

Reliable:

Uniform force during opening and closing

Ideal where space is restricted:

Slim design supports safe operation

Optimum stability:

Conical clamping arm with U-profile

Safe application:

Nothing catches on the smooth edges

Fast and flexible:

Easy retrofitting thanks to a wide range of accessories

Ergonomic and slip-resistant:

Easy to operate wearing work gloves

Non-reflecting

The NITROX-SURFACE is ideal for use with laser devices

Safe when opening:

More space between clamping arm and grip prevents pinching

Extremely compatible:

Oblong holes allows assembly on existing boreholes

Secure fixation and locking with safety lock:

The inner locking system is a completely revolutionary development. Nothing gets caught or stuck. Operation is easy even when wearing work gloves.



Operating principle of the safety locking mechanism:

Fig. 1:

Engaged.

No risk of injury thanks to revolutionary grip - no pinching or interfering contours.



Fig. 2:

Disengaged.

Pulling the grip releases the internal locking pin.

