

## Item description/product images



## Description

**Material:**

Housing anodised aluminium.

Bearing surface Frelon (Teflon plus proprietary fillers).

**Version:**

Linear plain bearing with Frelon coating.

**Note:**

Virtually chemically inert.

Self-lubricating (no additional lubrication required).

High temperature range (-240 °C to +260 °C).


Dampens vibrations.

High static load capacity - projected surface area x P ( $P = 1034 \text{ N/cm}^2$ )

Suitable for food, pharmaceutical, medical and chemical applications.

Insensitive to dirt.

## Drawings



## Overview of items

Order No.	Version 1	D	D1	G	L	L1	L2	W
21495-01-050	closed	5	12	-	22	14,28	1,14	-
21495-01-080	closed	8	16	-	25	16,28	1,14	-
21495-01-100	closed	10	19	-	29	22,04	1,32	-
21495-01-120	closed	12	22	-	32	22,64	1,32	-
21495-01-160	closed	16	26	-	36	24,64	1,32	-
21495-01-200	closed	20	32	-	45	31,26	1,63	-
21495-01-250	closed	25	40	-	58	43,8	1,9	-
21495-01-300	closed	30	47	-	68	51,8	1,9	-
21495-01-081	open	8	16	60°	25	16,28	1,14	5,1
21495-01-101	open	10	19	60°	29	22,04	1,32	6,4
21495-01-121	open	12	22	78°	32	22,64	1,32	7,6
21495-01-161	open	16	26	78°	36	24,64	1,32	10,4
21495-01-201	open	20	32	60°	45	31,26	1,63	10,8
21495-01-251	open	25	40	60°	58	43,8	1,9	13,2
21495-01-301	open	30	47	72°	68	51,8	1,9	14,2