


## Item description/product images

**Description****Note:**

Gauge unit suitable for measuring concentricity, run-out and perpendicularity. The robust design allows the unit to be used in the workshop and inspection room. A swivel contact roller simplifies positioning of the workpiece. The light sliding guides allow the dial gauges to be placed anywhere.

**Technical data:**


Inspection range  $\varnothing$  5 mm to  $\varnothing$  80 mm  
Roller spacing min. 29 mm, max. 89 mm.  
Carriage travel max. 100 mm.  
Contact roller thrust is adjustable.  
Gear driven rollers.

Roller precision: parallelism and coaxialism of both rollers max. 2  $\mu$ m.

Base plate granite: 300 mm x 130 mm x 25 mm

## Drawings

*slide, prism, dial  
gauge holder and dial  
gauge not included*



## Overview of items

Order No.	Article description
32506-01	CONCENTRICITY GAUGE